

## Alternative to GL13 (includes Hyne LGL)

Prolam® sizes are based on equivalent deflection. These tables are for guidance only, and any Prolam substitution should be verified against the complete selection chart or the Prolam online specifier. [specifier.prolamnz.com](http://specifier.prolamnz.com). Alternatives may not be suitable for all situations.

GL13 E = 13.3GPa	Prolam PL8 Alternative	Prolam PL12 Alternative
140 x 42	190 x 42 or 140 x 88	140 x 63 or 190 x 42
190 x 42	240 x 42 or 190 x 88	190 x 63 or 240 x 42
240 x 42	290 x 42 or 240 x 88	240 x 63 or 290 x 42
290 x 42	315 x 63 or 290 x 88	290 x 63 or 315 x 42
315 x 42	360 x 63 or 290 x 88	290 x 63 or 360 x 42
360 x 42	360 x 88	360 x 63 or 405 x 42
405 x 42	405 x 88	405 x 63
140 x 63	190 x 42	140 x 88 or 190 x 42
190 x 63	240 x 63	190 x 88 or 240 x 63
240 x 63	290 x 63	240 x 88 or 290 x 42
290 x 63	315 x 88	290 x 88 or 315 x 63
315 x 63	360 x 88	315 x 88 or 360 x 63
360 x 63	405 x 88 or 450 x 63	360 x 88 or 405 x 63
405 x 63	450 x 88	405 x 88 or 450 x 63
140 x 90	190 x 63	190 x 42
190 x 90	240 x 88	240 x 63
240 x 90	290 x 88	290 x 63
290 x 90	360 x 88	315 x 88
315 x 90	405 x 88	360 x 88
360 x 90	450 x 88	405 x 88
405 x 90	495 x 88	450 x 88

This schedule applies only to Prolam products