

# Alternative to hySPAN or LVL13

Prolam® sizes are based on equivalent deflection. These tables are for guidance only, and any Prolam substitution should be verified against the complete selection chart or the Prolam online specifier. [specifier.prolamnz.com](https://specifier.prolamnz.com). Alternatives may not be suitable for all situations.

hySPAN E = 13.2GPa	Prolam PL8 Alternative	Prolam PL12 Alternative
150 x 45	190 x 42 or 140 x 88	140 x 63
170 x 45	240 x 42 or 190 x 63	190 x 42
200 x 45	240 x 42 or 190 x 88	190 x 63
240 x 45	290 x 42 or 240 x 88	240 x 63
300 x 45	315 x 63 or 290 x 88	290 x 63
360 x 45	360 x 88	360 x 63
400 x 45	405 x 88	405 x 63
150 x 63	190 x 63	140 x 88
170 x 63	190 x 88 or 240 x 42	190 x 63
200 x 63	240 x 63	190 x 88
240 x 63	290 x 63	240 x 88
300 x 63	315 x 88 or 360 x 63	290 x 88
360 x 63	405 x 88 or 450 x 63	360 x 88
400 x 63	450 x 88	405 x 88
600 x 63	N/A	595 x 88
150 x 90	190 x 88	190 x 63
170 x 90	240 x 63	240 x 42
200 x 90	240 x 88	240 x 63
240 x 90	315 x 88	290 x 63
300 x 90	360 x 88	315 x 88
360 x 90	450 x 88	405 x 88
400 x 90	495 x 88	450 x 88

This schedule applies only to Prolam products